


ELECTRICAL SPECIFICATION

	FREE LOAD	ON LOAD
VOLTAGE (V)	3.0	3.0
CURRENT (AMP)	0.152 MAX	0.67 MAX
SPEED (R.P.M.)	5600~6800	3600~4300
TORQUE (G-CM)	---	15.5

CONFIRMED & ACCEPTED BY: **2 APR 1993**

Co, Chop Signature & Date



NOTE:

1. ONLY WHEN SHAFT IS IN EXTREME LEFT POSITION.
2. ENDPLAY LIMITS OF SHAFT 0.6mm MAX.

REF: S.D.NG. 13272 C3
CUSTOMER CODE:

ITEM		VISION		DATE TESTED		APPROD	
FINISHING		TOLERANCE EXCEPT AS NOTED		DECIMAL & TOLERANCE IN MILLI		ANGLES	
MATERIAL		TITLE		PART NO.		DIVG. NO.	
Sun Motor Mfg. Ltd.		S18-18130-38C		450-015		0	
新伸隆打製造有限公司		CHECKED		APPROD		SCALE	
DRN		DESIGN		APPROD		SCALE	