





QUEST CABLING SOLUTIONS CAT6A 550MHZ FTP 60°C ISO/IEC 11801& EN50288 & ANSI/TIA-568C.2
ETL/3P VERIFIED - 24AWGX4P PATCH TYPE CMR ROHS


W/OR 1 1 W/OR
OR 2 2 OR
W/GR 3 3 W/GR
GR 6 6 GR
BL 4 4 BL
W/BL 5 5 W/BL
W/BR 7 7 W/BR
BR 8 8 BR



NPC-8XXX
LENGTH
COLOR

COLOR(X)	
BLUE	2
GRAY	9

Length: 3', 7', 10', 15', 25'



9			
8			
7			
6			
5			
4			
3	60P PVC XXXX MOLDED	12	g
2	8P8C MALE GOLD PLATED PIN 50U"	2	pcs
1	CABLE:(7C/0.20BC±0.02BC+HDPE0.88)*4P+DIVIDER+MYLAR+(1C/0.52TD)DRAIN WIRE+AL-FOIL(双面)+OD:6.4±0.2MM	1	pcs
NO	Description	Q,TY	Unit

 Quest Technology Int'l, Inc. 11200 NW 138th St, Medley, FL 33178 Tel: 305-613-9583 Fax: 305-613-9576 www.QuestTechnology.com				DESCRIPTION	CAT6A FTP PATCH CORD	SCALE	FIT	UNITS:MM	3RD ANGLE
APPROVED	CHECKED	DRAWING	DESIGNED	MODEL NO	NPC-8XXX				
				DRAWING NO	SRT6A-M45-XX-XX				
				FINISHING			2014.05.09		A1
				MATERIAL		SYM	DATE		REVISION