



- Square caps
- Different top surfaces: flat, convex or concave
- 14.3 mm x 14.3 mm
- h = 19.1 mm; 20.2 mm; 20.1 mm
- Material: ABS/polycarbonate
- Temp. Range:
 - Solid cap: -40/+65°C
 - Transparent cap: -40/+85°C
- Panel cut-out: 1KS/1KBS/1KCS-14.7 x 14.7




Custom solution

DIMENSIONS


SMD w/LED + 1KS




TH w/LED + 1KBS



SMD w/LED + 1KCS



Bezel (optional)



ILLUMINATED – HOW TO ORDER

Switch	Mounting	Actuation force	LED	Cap	Bezel
5 G					
	TH9 through-hole	20	01 blue	Frosted white lens and transparent lid	03 grey
	SH9 surface mount	35	22 green		06 white
		65	42 yellow		08 red
		Q*	61 white	1KS 	1KCS 
			82 red	1KBS 	09 black
			2242 green/yellow		
			8222 red/green		
			8242 red/yellow		

*For an illuminated quiet 2.0N switch add Q

*For an illuminated quiet 2.0N switch add Q to the end of the switch part number.

NON-ILLUMINATED—HOW TO ORDER

Switch	Mounting	Actuation force	Cap	Bezel
5 G			1 K S 1 6	2 K
TH9 through-hole	20		Frosted white lens	03 grey
SH9 surface mount	20Q		1KS 	06 white
	35			08 red
	65			09 black

Ordering example:

5GTH93501+1KCS1116+2K09 with illumination OR 5GSH965+1KS09+2K03 without illumination OR *5GTH92082Q (illuminated quiet version)

Please see colour codes, updates of products and changes of specifications on www.mec.dk