


CASE FINISH	CURRENT (AMPS)	WORKING VOLTAGE				MAXIMUM DC RESISTANCE (OHMS)	MAXIMUM VOLTAGE DROP		MINIMUM CAPACITANCE (uF)	MIN. INSERTION LOSS PER MIL-STD-220 FULL LOAD, +25°C													
		-55°C TO +85°C		-55°C TO +125°C			DC	AC		14 KHz	30 KHz	50 KHz	75 KHz	100 KHz	150 KHz	300 KHz	500 KHz	1 MHz	10 MHz	100 MHz	1 GHz	10 GHz	
		AC	DC	AC	DC		DC	AC		DC	DC	DC	DC	DC	DC	DC	DC	DC	DC	DC	DC		
SOLDER	1	125@400Hz	350	125@400Hz	300	0.250	0.25	---	0.30	--	--	--	--	--	23	43	--	70	70	--	70	--	

#### PART MARKING:

M15733/54-0012  
0LSP2 DATE CODE  
300VDC 1A 125°C  
125VAC 400Hz  
51-311-415



PACKAGE MARKING:

## STANDARD

#### MARKING NOTES:

N/A

## SCHEMATIC



## MTG. HARDWARE

## NOTES:

1) MOUNTING TORQUE NOT TO EXCEED 7 in-lbs.

Quality Products From The Specialists In Electro-Magnetic Compatibility

Quality Products From The Specialists In Electro-Magnetic Compatibility

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[51-311-415](#)