






① HOUSING MATERIAL: LIQUID CRYSTAL POLYMER.
COLOR: NATURAL.


② CONTACT MATERIAL: PHOSPHOR BRONZE.

③ CONTACT FINISH:(D)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
FLASH GOLD PER ASTM B 488, OVER
0.00076 MIN PALLADIUM-NICKEL OVER UNDERPLATE, OR
0.00076 MIN GOLD PER ASTM B 488 OVER UNDERPLATE.
ON LEADS:
0.00127 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.


④ PART MARKING LOCATED APPROXIMATELY AS SHOWN.



5536699-1 AS SHOWN




SECTION A-A
SCALE 6:1



PART NUMBER 5536699-J						
D		AC			AA	D
C		AC			AA	C
B		AC			AA	B
A		AC			AA	A
ROW	1	2	3	4	5	6 ROW
	POSITION					
	CONTACT LOAD CHART					

	5536699-3
	5536699-2
	5536699-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		PIN CHAD BAKER 10-07-98 CHK CHAD BAKER 10-07-98 APP'D D. KOVALICK 10-10-98	ttyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm 		NAME PIN ASSY,POWER,VERTICAL,Z-PACK 2mm FB, PRESS FIT LEADS,SEQUENCED		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.13 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± ±		PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		
MATERIAL 		SIZE A1 00779 C-5536699		
FINISH 		DRAWING NO C-5536699		
CUSTOMER DRAWING 		SCALE 4:1 SHEET 1 OF 1 REV 0		