

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200910012](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Attachable Connectors, 90° Angle Male, 4 Poles

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [120091](#)
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Nano-Change \(M8\) Products](#)
Product Name Nano-Change (M8)
Type Field Attachable Connector
UPC 78678832516

Physical
Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender Male
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Net Weight 10.432/g
Orientation 90° Angle
Poles 4
Temperature Range - Operating 0°C to +80°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 4.0A
Voltage - Maximum 60V AC / 75V DC

Material Info
Engineering Number N04MA04124

Reference - Drawing Numbers
Sales Drawing SD-120091-004



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[120091](#) Series