


Straight Blade Devices


15 and 20 Ampere, 125 Volts

2 Pole, 3 Wire Grounding


Insulgrip® Flanged Inlets and Receptacles




HBL5278C




HBL61CM64



HBL5279C



HBL5256




HBL61CM65

15A 125V
NEMA 5-15P
UL CSA20A 125V
NEMA 5-20P
UL CSA

Flanged Inlets

Description	Catalog Numbers	
Nylon casing, back wired.	HBL5278C	HBL5378C
Weatherproof, gray, with lift cover and multiple drive screws.	HBL61CM64	
Weatherproof, black, with lift cover and boot, multiple drive screws.	HBL61CM64BK	-
Stainless steel flange, phenolic body, miniature style, for molded on connectors only, multiple drive screws.	HBL5240*	-

Notes: *Specially designed to accept "molded-on" connector bodies. Catalog number HBL5240 will not accept re-wireable size connector bodies listed in this catalog or molded connectors having a "rejection obstruction" as required by Underwriters Laboratories Inc. standard #817 cord sets and power supply cords" effective 7/1/81. See page A-45 for accessories.

15A 125V
NEMA 5-15R
UL CSA
0.5 HP20A 125V
NEMA 5-20R
UL CSA
1 HP

Flanged Receptacles

Description	Catalog Numbers	
Nylon casing, back wired.	HBL5279C	HBL5379C
Stainless steel flange, phenolic body, covered terminals, multiple drive screws.	HBL5279	-
Stainless steel flange, brown phenolic (mounting screws packed separately).	HBL5256	-
Weatherproof, gray nylon, with lift cover and boot, multiple drive screws.	-	HBL61CM65*

Notes: *Not CSA Certified.
See page A-45 for accessories.