




FEATURES:

- ✓ This retractable sheath banana plug has a stacking feature allowing the insertion of standard or other retractable plugs

MATERIALS:

Retractable Sheath Banana Plug:

Spring – Beryllium Copper per QQ-C-533, Alloy 172, Cond. HT.

Plug Body – Brass per QQ-B-626, Alloy 360, ½ hard

Compression Spring – Stainless Steel, Alloy 302

Spring and Plug Body Finish:

Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Plug Body Insulation:

Polypropylene molded to plug body and wire. Color matches color of wire.

Wire and Insulation:

18 AWG, stranding 65 x 36 T.C., .144" (3.66mm) O.D, PVC.



RATINGS:

Operating Voltage: Hands free usage in controlled voltage environments: 1200 Vrms maximum. *For CE compliance:* not intended for hand-held use at voltages above 33 Vrms/70 Vdc.

Operating Temperature: +131°F (+55°C) Max.

Current: 7 Amperes.

ORDERING INFORMATION: Model 5403-Length-Color

Length =: 12" (30,48cm), 24" (60,96cm), 36" (91,44cm), 48" (121,92cm), 60" (152,4cm)

Color =: 0 (Black), 2 (Red)

For custom lengths and colors, contact Technical Support at custom@pomonatest.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)

For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com