

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'F5D4-4M1Y'

Your search criteria matched only one product, shown below

F5D4-4M1Y



- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

*Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FXE10-10M1Y) with the desired length (FXE10-10M2Y for 2 meter length). The above lengths are stock items. For other lengths, contact Customer Service for actual lead times.

• Part Number	F5D4-4M1Y
• RoHS Compliancy Status	Compliant
• Note	F5D4-4M1Y replaces F5D4-4M1
• Part Description	FC to FC multimode duplex patch cord (two FC connectors on each end) - 50/125µm.
• Product Type	FC Patch Cords
• Length (m)	1
• Fiber Compatibility	50/125µm
• Fiber Cable Size	3mm
• Fiber Cable Type	Jacketed
• Fiber Type	Multimode
• Cable Color	Orange
• Cable Type	Duplex
• CE Compliant	No
• Connector 1 Type	FC Connector
• Connector 2 Type	FC Connector
• End Configurations	FC to FC
• Fiber Count	2
• Flammability Rating	Riser (OFNR)
• Pricing Description	PC FC To FC 50µm Dupl 1m
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.