

APPLIANCE COUPLERS

Cordsets

IEC / EN 60320-1 / C13,
protection class I, pin
temperature 70 °C (cold
condition)



**Medical Grade
Standard
NEMA 5-15P**


IEC/EN 60320-1/C19



**North America
Standard
NEMA 5-15**



C7 Non-Polarized



C7 Polarized



C5 Polarized



**North America, Europlug, United Kingdom, Schuko
Standards
NEMA 1-15P, 5-15P, CEE 7/7, 7/16, BS 1363**



Cord Type SJT Conductor 3 x 18 AWG Rated 10 A / 125, 250 V 15 A / 125 V Color clear Length 10 feet 4300	Cord Type SJT Conductor 3 x 14 AWG Rated 16 A / 250 V Color black Length 2,5 meters 6016	CS01.0221.150 C7 Non-Polarized standard 2.5 A / 250 V Nema 1-15P SPT2 CS02.0221.150 C7 Polarized standard 7 A / 250 V Nema 1-15P AWG18 CS01.0121.150 C7 Non-Polarized H03VVH2-F 2.5 A / 250 V Europlug CEE 7/16 CS01.0421.150 C7 Non-Polarized H03VVH2-F 2.5 A / 250 V UK BS 1363 CS03.0421.150 C5 Polarized H03VV-F 2.5 A / 250 V UK BS 1363 CS03.0521.150 C5 Polarized H03VV-F 2.5 A / 250 V Schuko Plug CS03.0621.150 C5 Polarized standard 2.5 A / 250 V North America SPT2 Nema 5-15P Color black, Length 1500 mm CS
---	--	---

Approvals / Cordsets supplied by SCHURTER carry the country specific approvals

4300.0920	6009.5195	CS01.0121.150 - CS03.0621.150
------------------	------------------	--------------------------------------