

MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED MFG CODE 81989

SWITCH - TOGGLE FLUSH KEY

CATALOG LISTING
1TP910 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.


CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON		
	LUG SIDE (1-2)	CENTER (1-2)	OPPOSITE LUG (2-3)
1TP910-1	ON	OFF	ON
1TP910-2	OFF	NONE	ON
1TP910-3	ON	NONE	ON
1TP910-21	NONE	OFF	ON
1TP910-31	NONE	ON	ON
1TP910-4	MOM OFF	NONE	ON
1TP910-5	MOM ON	OFF	ON
1TP910-6	MOM ON	NONE	OFF
1TP910-7	MOM ON	OFF	MOM ON
1TP910-8	MOM ON	NONE	ON
1TP910-51	NONE	ON	MOM ON
1TP910-61	MOM ON	OFF	NONE

ELECTRICAL DATA

L191 15A 125, 250, 277 VAC
1/2HP 125 VAC
1HP 250, 277 VAC
5A 125 VAC "L"



L192 10A 125, 250, 277 VAC
1/4HP 125 VAC,
1/2HP 250, 277 VAC
3A 125 VAC "L"



NOTES

- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
- 2 - FOR TERMINAL COVER SEE MICRO SWITCH CATALOG LISTING 5PA7
- 3 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F

THIRD ANGLE PROJECTION			
SCALE FULL			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE UNLESS NOTED. TOLERANCES ARE 2			
NO PLACES	DM	TOL	DM
ONE PLACE	mm	1/32	in
TWO PLACES	mm	0.001	in
THREE PLACES	mm	0.0005	in
ANGLES			
DESIGN UNITS		US CUSTOMARY	
WEIGHT		.10 LB EST.	