

SWITCH-TOGGLE

11TW19 SERIES CHART 3

11TW19 SERIES


DRAWING NUMBER
X 2
X 3
X 4
X 5
X 6
X 7
X 8
X 9
X 10

REVISIONS

A 0027404
L S D
13 MAY 70
B 0027821
0027850
3 SEP 70
C 43472
M M M
5 MAY 81
D 0050565
L R F
12 DEC 81
E 0053650
K E W
10 OCT 83
F 54927
O R T
12 MAY 84
G PR-13896
J A S
20 MAY 85
H 0061252
J A P
16 MAR 87
J 0062939
T S K
24 FEB 88

KAS 13 APR 70
DRAWN
PC-60379-001


.072 WIDE X .030 DEEP
KEYWAY



NOTE -
1 FURNISHED UNASSEMBLED
2-TERMINALS ARE PLATED FOR
SOLDERING
3 MATTE FINISH
4 BRIGHT FINISH
5 SUFFIX MUST BE ADDED FOR DESIRED
LEVER STYLE AND COLOR. (EXAMPLE:
11TW19-1-A001)


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE 2 TO 1
	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
		UNLESS OTHERWISE NOTED
		DIMENSIONS ARE IN INCHES
		TOLERANCES ARE:
		ONE PLACE (.0)
		TWO PLACE (.00)
		THREE PLACE (.000)
		ANGLES 1
		WEIGHT .025 LB MAX



CATALOG LISTING	ONE EXTREME POSITION (KEYWAY) 2-1	CENTER POSITION	OTHER EXTREME POSITION (OPPOSITE KEYWAY) 2-3
11 TW19-1	ON	OFF	ON
11 TW19-2	OFF	NONE	ON
11 TW19-3	ON	NONE	ON
11 TW19-5	MOM ON	OFF	ON
11 TW19-7	MOM ON	OFF	MOM ON
11 TW19-8	MOM ON	NONE	ON

LEVER STYLE



LEVER COLOR CODE 5

COLOR IDENT	COLOR	COLOR IDENT	COLOR	COLOR IDENT	COLOR
001	WT-07 WHITE				
002	BK-09 BLACK				
003	BL-05 BLUE				
004	RD-08 RED				
005	GN-08 GREEN				
006	OR-06 ORANGE				
007	GY-95 GRAY				