

1. MATERIALS AND FINISHES:
BODY - ZINC DIE CAST, NICKEL PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING (.000003 THICK)
@ CONTACT AREA ONLY, TIN PLATING AT TAIL, NICKEL PLATED OVERALL
INSULATOR - POLYPROPYLENE
HOUSING - PBT, BLACK
ROUND PIN - BRASS, TIN PLATING
GROUNDNG TERMINAL - STEEL, TIN PLATING
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 1 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -55° C TO 85° C
4. PACKAGING:
A. PACKAGED IN PACKING TRAYS
B. QUANTITY PER TRAY: 40
5. SEPERATLY SUPPLIED MOUNTING HARDWARE
TO BE TIGHTENED TO 10 IN-LBS MIN/15 IN-LBS MAX
WHEN ASSEMBLING TO PANEL

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	12/7/90	37726	DR
H	SEE SHEET I	2/3/05	45257	CPM
J	UPDATED FORMAT AND NOMINAL ENVELOPE DIMENSIONS	7/15/13	49574	EW

