


## 24-outlet Vertical Power Strip with 15-ft. Cord

MODEL NUMBER: **PS7224**



### Description

Tripp Lite's PS7224 power strip offers 15 amp, 120V multi-outlet AC power distribution in a convenient 72 inch mountable housing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications. Includes 24 NEMA 5-15R output receptacles with 2.795 inch center-to-center spacing, 15 ft AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 24 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: 72 in. corded, mountable power strip

### Features

- Sturdy all-metal 72 inch corded strip format with 2.795 inch center-to-center outlet spacing
- Included mounting hardware
- Includes 24 NEMA 5-15R output receptacles
- Lighted power switch with locking transparent cover prevents accidental shutoff
- 15 amp electrical capacity with circuit breaker
- 120VAC, 50/60Hz electrical compatibility

## Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800

### Highlights

- 24 outlets
- Convenient and safe covered, on/off switch
- 15-amp circuit breaker
- 15 ft. cord
- 72" length

### Applications

- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications

### Package Includes

- PS7224
- Mounting hardware
- Instruction manual

Circuit Breaker (amps)	15
Outlet quantity / type	24 Nema 5-15R
Outlet spacing	2.795 in.
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	Nema 5-15P
Input plug features	Black
Input cord length (ft.)	15
Input cord length (m)	4.572
Input cord gauge, type	14/3 SJT
Voltage compatibility (VAC)	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Lighted 2 position switch controls power to all outlets
Locking switch cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Unit Dimensions (HWD/in)	72 x 1.5 x 1.5
Unit Dimensions (HWD/cm)	183 x 3.8 x 3.8
Unit weight (lbs)	5.5
Unit weight (kg)	2.497
Material of construction	Aluminum
Mounting accessories included	Includes mounting clips
Receptacle Color	Black
AC line cord color	Black
Style	Bench/Cabinet Mount
Form factors supported	Supports horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
Outlets center to center measurement	72mm
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## WARRANTY

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[PS7224](#)