


二段裏蝶番

CONCEALED 2-STEP HINGES






B-104-1

[B-104-2・B-104-3]



[B-104-1]



商品番号 Product No.	RoHS 2D/3D	CAD 3D	L ₁	L ₂	L ₃	L ₄	W ₁	W ₂	W ₃	(H ₁)	H ₂	(H ₃)	H ₄	H ₅	(H ₆)	t ₁	t ₂	ΦD ₁	(ΦD ₂)	製品質量(g) Mass	コード Code	単価 Price	量販価格 Quantity	Bulk Price 単価 Price
B-104-1	●	2D/3D																		240	10262	¥580	30個～	¥557
B-104-2	●	3D	70	40	45	75	20	40	20	30	6.5	21	12	6	15	2.3	3.2	6	13	165	10263	¥400	30個～	¥384
B-104-3	●	2D/3D	54	30	35	57	15	31	15	22	4.5	15.5	10	4.5	11	2	2.3	4	9	75	10264	¥340	30個～	¥326

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

図面による See the drawings

特徴 Feature

- 扉は160°以上開閉しボックスの前面が広く使えます。
- Door opens/closes more than 160° for wide frontal clearance on box.

仕様 材質: 冷間圧延鋼板 (SPCC)

表面仕上: 亜鉛めっきクロメート処理
(MFZn-C)

用途 配分電盤・計測機器・通信機器

納期 標準在庫品

Specifications: Material: Cold rolled steel plate (SPCC)

Finish: Zinc plating chromate treatment (MFZn-C)

Specific use: Distribution boards, measuring and communication equipment

