

# General Purpose - Rapid Rack (C2RR Series)



**Rapid Rack  
POPULAR STOCKED CONFIGURATIONS  
(See Page 53 For Component Parts)**

## FEATURES

- Heavy duty - welded frame - recommended maximum weight (C2F247836 tested) - 1,500 pounds (682 kg)
- Unit is shipped complete (**NO ASSEMBLY REQUIRED**)
- Choice of two depths 23.63" (600 mm) - 21.63" (549 mm) usable depth or 31.5" (800 mm) - 29.5" (749 mm) usable depth
- Standard 19" panel width - 23" (584 mm) overall
- **Unit includes:**
  - a welded steel rack frame
  - two (2) removable side panels (with 1/4 turn latches)
  - four (4) infinitely adjustable, tapped combination rack mount rails (full E.I.A. spacing)
  - one (1) solid flush mount door (can be either front or back as rack is symmetrical) - locking with two (2) keys
  - solid top
  - four (4) leveling feet
- Heavy duty 14 gauge steel frame
- Formed 16 gauge steel side panels are recessed to fit flush with the sides of the cabinet
- Welded corner reinforcements
- Opening in bottom for cable entry
- Panel rails are zinc plated, 10 gauge steel, drilled and tapped 10-32
- Finished in a rugged, textured powder paint

## UNIVERSAL ACCESSORIES

- Rack panels [Page 90](#)
- Ventilated rack panels [Page 92](#)
- Panel mount doors & chassis [Page 94](#)
- Shelves & slides [Page 95](#)
- Drawers [Page 101](#)
- Cable management [Page 102](#)
- Cooling [Page 105](#)
- Rack mount outlet strips [Page 110](#)
- Hardware [Page 127](#)
- Exclusive to this series [Page 53](#)
- Visit our web site for our most [recent accessories](#)

**ASSEMBLED**  
*Shipped on its own skid  
for handling ease &  
protection  
FROM STOCK!*



Assembled

Welded



### CANADA

Guelph, Ontario (519) 822-2960  
St. Laurent, Quebec (514) 343-9010

### USA

Cheektowaga, NY (716) 630-7030



### EUROPE


Basingstoke, UK 01256 812812

### AUSTRALIA


Queenstown SA, Australia 61-8-8240-2244

# General Purpose - Rapid Rack (C2RR Series)


Front View




Side View  
(Side Panel  
Not Shown)



Bottom View



Top View  
(Top Cover  
Not Shown)



23.63" (600 mm) Deep - Usable Depth = 21.63" (549 mm)

| Part Number    |                     | Panel Height |       | Overall Dimensions |                |                   | Weight        |
|----------------|---------------------|--------------|-------|--------------------|----------------|-------------------|---------------|
| Black Textured | Light Gray Textured | Inches       | Units | Height (A)         | Width (B)      | Panel Opening (D) |               |
| C2RR194223BK1  | C2RR194223LG1       | 42"          | 24U   | 49.31" (1,252 mm)  | 23.0" (584 mm) | 42.06" (1,068 mm) | 170# (77 kg)  |
| C2RR196323BK1  | C2RR196323LG1       | 63"          | 36U   | 70.31" (1,786 mm)  | 23.0" (584 mm) | 63.06" (1,602 mm) | 218# (99 kg)  |
| C2RR197023BK1  | C2RR197023LG1       | 70"          | 40U   | 77.31" (1,964 mm)  | 23.0" (584 mm) | 70.06" (1,780 mm) | 230# (105 kg) |
| C2RR197823BK1  | C2RR197823LG1       | 78.75"       | 45U   | 86.06" (2,186 mm)  | 23.0" (584 mm) | 78.81" (2,002 mm) | 254# (116 kg) |

31.5" Deep (800 mm) - Usable Depth = 29.5" (749 mm)

| Part Number    |                     | Panel Height |       | Overall Dimensions |                |                   | Weight        |
|----------------|---------------------|--------------|-------|--------------------|----------------|-------------------|---------------|
| Black Textured | Light Gray Textured | Inches       | Units | Height (A)         | Width (B)      | Panel Opening (D) |               |
| C2RR194231BK1  | C2RR194231LG1       | 42"          | 24U   | 49.31" (1,252 mm)  | 23.0" (584 mm) | 42.06" (1,068 mm) | 194# (88 kg)  |
| C2RR196331BK1  | C2RR196331LG1       | 63"          | 36U   | 70.31" (1,786 mm)  | 23.0" (584 mm) | 63.06" (1,602 mm) | 250# (114 kg) |
| C2RR197031BK1  | C2RR197031LG1       | 70"          | 40U   | 77.31" (1,964 mm)  | 23.0" (584 mm) | 70.06" (1,780 mm) | 268# (122 kg) |
| C2RR197831BK1  | C2RR197831LG1       | 78.75"       | 45U   | 86.06" (2,186 mm)  | 23.0" (584 mm) | 78.81" (2,002 mm) | 290# (132 kg) |

EUROPE

Basingstoke, UK 01256 812812

AUSTRALIA

Queenstown SA, Australia 61-8-8240-2244



CANADA

Guelph, Ontario (519) 822-2960  
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 630-7030



Assembled

Welded