




- VDC: 5, 12, 24
- RPM: 2600~6200
- CFM: 2.27~5.64
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 15g




## DC FAN

40x40x11mm

### Specification

|           | Bearing                                              | Voltage | Current   | Speed     | Input Power | Air Flow  | Static Pressure       | Noise     | Weight |
|-----------|------------------------------------------------------|---------|-----------|-----------|-------------|-----------|-----------------------|-----------|--------|
| MODEL NO  | ○ Sleeve<br>● One ball and one sleeve<br>○ Hydraulic | (Vdc)   | (Amp)     | (Rpm)     | (Watts)     | (CFM)     | (mm/H <sub>2</sub> O) | dB(A)     | Gram   |
| B4010B12L | ●                                                    | 12      | 0.06      | 4200      | 0.72        | 3.71      | 1.82                  | 22.6      | 15     |
| B4010S12L | ○                                                    | 12      | 0.06      | 4000      | 0.72        | 3.67      | 1.52                  | 21.8      | 15     |
| B4010B12M | ●                                                    | 12      | 0.07      | 5200      | 0.84        | 4.48      | 2.60                  | 30.2      | 15     |
| B4010B12H | ●                                                    | 12      | 0.07      | 6200      | 0.84        | 5.64      | 3.88                  | 31.2      | 15     |
| C4010B05L | ●                                                    | 5       | 0.08      | 4200      | 0.40        | 3.71      | 1.82                  | 22.6      | 15     |
| C4010S05L | ○                                                    | 5       | 0.08      | 4000      | 0.40        | 3.67      | 1.52                  | 21.8      | 15     |
| C4010B05M | ●                                                    | 5       | 0.15      | 5200      | 0.75        | 4.48      | 2.60                  | 30.2      | 15     |
| C4010B05H | ●                                                    | 5       | 0.16      | 6200      | 0.80        | 5.64      | 3.88                  | 31.2      | 15     |
| C4010B12L | ●                                                    | 12      | 0.06      | 4200      | 0.72        | 3.71      | 1.82                  | 22.6      | 15     |
| C4010S12L | ○                                                    | 12      | 0.06      | 4000      | 0.72        | 3.67      | 1.52                  | 21.8      | 15     |
| C4010B12M | ●                                                    | 12      | 0.07      | 5200      | 0.84        | 4.48      | 2.60                  | 30.2      | 15     |
| C4010B12H | ●                                                    | 12      | 0.10      | 6200      | 1.20        | 5.64      | 3.88                  | 31.2      | 15     |
| C4010B24L | ●                                                    | 24      | 0.06      | 4200      | 1.44        | 3.71      | 1.82                  | 22.6      | 15     |
| C4010S24L | ○                                                    | 24      | 0.06      | 4000      | 1.44        | 3.67      | 1.52                  | 21.8      | 15     |
| C4010B24M | ●                                                    | 24      | 0.07      | 5200      | 1.68        | 4.48      | 2.60                  | 30.2      | 15     |
| C4010B24H | ●                                                    | 24      | 0.08      | 6200      | 1.92        | 5.64      | 3.88                  | 31.2      | 15     |
| D4010B05L | ●                                                    | 5       | 0.11      | 4200      | 0.55        | 3.71      | 1.82                  | 22.6      | 15     |
| D4010S05L | ○                                                    | 5       | 0.11      | 4000      | 0.55        | 3.67      | 1.52                  | 21.8      | 15     |
| D4010B05M | ●                                                    | 5       | 0.13      | 5200      | 0.65        | 4.48      | 2.60                  | 30.2      | 15     |
| D4010B05H | ●                                                    | 5       | 0.15      | 6200      | 0.75        | 5.64      | 3.88                  | 31.2      | 15     |
| D4010B12L | ●                                                    | 12      | 0.06      | 4200      | 0.72        | 3.71      | 1.82                  | 22.6      | 15     |
| D4010S12L | ○                                                    | 12      | 0.06      | 4000      | 0.72        | 3.67      | 1.52                  | 21.8      | 15     |
| D4010B12M | ●                                                    | 12      | 0.07      | 5200      | 0.84        | 4.48      | 2.60                  | 30.2      | 15     |
| D4010B12H | ●                                                    | 12      | 0.10      | 6200      | 1.20        | 5.64      | 3.88                  | 31.2      | 15     |
| D4010B24L | ●                                                    | 24      | 0.06      | 4200      | 1.44        | 3.71      | 1.82                  | 22.6      | 15     |
| D4010S24L | ○                                                    | 24      | 0.06      | 4000      | 1.44        | 3.67      | 1.52                  | 21.8      | 15     |
| D4010B24M | ●                                                    | 24      | 0.07      | 5200      | 1.68        | 4.48      | 2.60                  | 30.2      | 15     |
| D4010B24H | ●                                                    | 24      | 0.08      | 6200      | 1.92        | 5.64      | 3.88                  | 31.2      | 15     |
| E4010B12H | ●                                                    | 12      | 0.06~0.15 | 2600~5200 | 0.72~1.80   | 2.27~4.48 | 0.84~2.60             | 22.9~30.2 | 15     |
| F4010B12L | ●                                                    | 12      | 0.06      | 4200      | 0.72        | 3.71      | 1.82                  | 22.6      | 15     |
| F4010S12L | ○                                                    | 12      | 0.06      | 4000      | 0.72        | 3.67      | 1.52                  | 21.8      | 15     |
| F4010B12M | ●                                                    | 12      | 0.07      | 5200      | 0.84        | 4.48      | 2.60                  | 30.2      | 15     |
| F4010B12H | ●                                                    | 12      | 0.10      | 6200      | 1.20        | 5.64      | 3.88                  | 31.2      | 15     |



Design specifics subject to change without notice.

### STATIC PRESSURE

