




FEATURES:

- Spade lug attaches securely to a screw terminal while the medium size alligator test clip can quickly grab onto terminal points.
- Spade lug and alligator bodies are nickel plating for tarnish resistance
- The alligator features a flex boot for insulation protection.
- Alligators clip has .187" (4.75mm) max. jaw opening.

MATERIALS:

Alligator:Body: Steel, Nickel Plated

Spring: Stainless Steel

Flex Boot: Vinyl

Wire: 18 AWG, Stranding: 65 X 36 tinned copper, PVC Insulation, .144" (3.66 mm) O.D.

Marking: "POMONA 1960-XX"

Spade Lug: Body: Brass, Nickel Plated

Insulation: Polypropylene molded to the spade lug and wire. Color matches wire.

RATINGS:

Operating Voltage: 150 VRMS

Current: 5 Amperes

Operating Temperature: +50°C (+122°F)

ORDERING INFORMATION: Model 1960-XX-*

XX = Length in inches

Standard Lengths: 4" (10.16cm), 8" (20.32cm), 12" (30.48cm), 24" (60.96cm), 36" (91.44cm), 48" (121.92cm) & 60" (152.40cm). Additional lengths can be quoted upon request.

* = Color of Flex Boot and Wire, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1960-36-0](#) [1960-36-2](#)