

70 Diagonal Cutters

DIN ISO 5749



70 01 160



70 02 160



70 05 160



70 06 160

- ▶ the indispensable diagonal cutter for all-round use
- ▶ high quality material and precise workmanship for long service life
- ▶ precision cutting edges for soft and hard wire
- ▶ clean cutting at cutting edge tips; also in case of thin copper wires
- ▶ cutting edges additionally induction hardened, cutting edge hardness approx. 62 HRC
- ▶ narrow head style for use in confined areas
- ▶ Vanadium electric steel, oil-hardened and tempered

Style 0:

- ▶ with bevel

Style 1:


- ▶ with bevel
- ▶ with opening spring

Style 2:

- ▶ with small bevel

special


The cutting edges of KNIPEX Diagonal Cutters – made of Vanadium steel – have a long service life, are machined highly precise and are very sharp – for a clean cut of soft and hard wires.



Article-No.	EAN-	Style	Head	Handles	Cutting capacities				
Length mm	Code 4003773-				 Ø mm	 Ø mm	 Ø mm	g	
70 01	110	014324		polished	plastic coated	3.0	2.0	1.2	80
	125	013402				3.0	2.3	1.5	90
	140	013419				4.0	2.5	1.8	125
	160	013426				4.0	2.8	2.0	175
	180	018070				4.0	3.0	2.5	200
70 02	125	034025		polished	with two-colour dual component handles	3.0	2.3	1.5	115
	140	023098				4.0	2.5	1.8	155
	160	034032				4.0	2.8	2.0	205
	180	034049				4.0	3.0	2.5	250
70 04	140	018100		chr. plated	chrome plated	4.0	2.5	1.8	105
70 05	125	039501		chrome plated	with two-colour dual component handles	3.0	2.3	1.5	115
	140	039488				4.0	2.5	1.8	155
	160	039600				4.0	2.8	2.0	205
	180	043706				4.0	3.0	2.5	250
70 06	125	018124		chrome plated	insulated with two-colour dual component handles  1000 V  	3.0	2.3	1.5	120
	140	040293				4.0	2.5	1.8	160
	160	021995				4.0	2.8	2.0	210
	180	033813				4.0	3.0	2.5	255
70 07	160	018155		chrome plated	plastic dipped insulated  1000 V   VDE-tested	4.0	2.8	2.0	240
	180	018179				4.0	3.0	2.5	285
70 11	110	018193		polished	plastic coated	3.0	2.0	1.2	80
70 15	110	029649		chrome plated	with two-colour dual component handles	3.0	2.0	1.2	105
70 26	160	018223		chrome plated	insulated with two-colour dual component handles  1000 V   VDE-tested	4.0	-	-	210



Cuts fine wires cleanly over the complete length of the blades



Slim head style and precise cut at blade tips: Advantageous when working in confined areas