


Part Number: 50240-7125

Ring Tongue Terminal for 14-16 AWG, Closed Un-insulated Brazed Barrel, Stud Size 5 (M3), Oxygen-Free Copper, Length 12.40mm, Clearance 5.20mm



Status: **OBsolete**
 Replacement: Contact Molex
 Series: 50240
 Category: Ring and Spade Terminals

[CHECK DISTRIBUTOR INVENTORY](#)
[Add to My Parts](#)
[Email this page](#)
Go to [Part Detail](#) ▾

Series image - Reference only

Specifications & Other Documents:

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com[EU ELV](#): Not Relevant[EU RoHS](#): Compliant[China RoHS](#): [REACH SVHC](#): Contains SVHC (2015 June 15): No[Low-Halogen Status](#): Low-Halogen[RoHS Certificate of Compliance \(PDF\)](#)[Multiple Part Product Compliance Form \(PDF\)](#)

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Hand Crimper For JIS Terminal	57257-5000
Hand Crimper For JIS Terminal	57343-5002

Crimp Quality Equipment

[Molex also offers wire strippers, pull testers, shut-height gauges, micro-meters and more](#)

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[COLLAPSE ALL](#)

▼ General

Status	Obsolete
Category	Ring and Spade Terminals
Series	50240
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
UPC	800753236851

▼ Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	512.000/mg
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	5 (M3)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	14, 16
Wire Size mm ²	1.04-2.63

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA	LR95446
UL	E134962

▼ Material Info

▼ Reference - Drawing Numbers

Product Specification	PS-50240-003
Sales Drawing	SD-50240-002

Molex Connectors

Wire-to-Board

Board-to-Board

Wire-to-Wire

Input/Output (I/O)

FFC/FPC

Sockets

Other Products

Optical Solutions

Antennas

Industrial Automation

Membrane Switches

Copper Flex

PCB Assemblies

Woodhead Electrical

Solid State Lighting

Application Tooling

Noise Suppression Sheets

Resources

Contact Us

Catalog

Cross-Reference

Industries

Literature

Product Name

Company Info

About Us

California Supply Chains Act

Careers

Compliance

ecocare

Investors

Press Room

Shows & Events

Supplier Portal

Other Info

Feedback

Help

Legal Disclaimer

Trademarks

View Mobile Site

Privacy Policy

Sitemap

Stay Connected with Molex:

