

Product Description

Enables the use of cable glands with smaller connection threads than the existing threaded holes



Application range

- Machines
- Devices
- Housings

Benefits

- Enables the use of cable glands with smaller connection threads than the existing threaded holes

Design

- Metric connection thread acc. to EN 50262

Technical Data
Material

Nickel-plated brass

Range of temperature

-60°C up to +200°C

Article List

Part number	Thread/ male M1	Thread/ female M2	Pieces / PU	Overall height mm	Thread length D mm	Outer Ø mm
SKINDICHT® MR-M						
52104310	16 x 1,5	12 x 1,5	100			
52104311	20 x 1,5	12 x 1,5	100			
52104312	20 x 1,5	16 x 1,5	100			
52104313	25 x 1,5	16 x 1,5	50			
52104314	25 x 1,5	20 x 1,5	50			
52104315	32 x 1,5	20 x 1,5	50			
52104316	32 x 1,5	25 x 1,5	50			
52104317	40 x 1,5	25 x 1,5	25			
52104318	40 x 1,5	32 x 1,5	25			
52104319	50 x 1,5	32 x 1,5	25			
52104320	50 x 1,5	40 x 1,5	10			
52104321	63 x 1,5	40 x 1,5	10			
52104322	63 x 1,5	50 x 1,5	10			
SKINDICHT® MR-M nickel plated brass, without hexagon						
52006575	72 x 2	63 x 1,5	1	19	12	78