

F

E

D

C

B

A

F





E

D

C

B

A



注記 NOTES

1. 材質 MATERIAL
ウエハー: PA (UL94V-0)
WAFER: PA, UL94V-0
ピン: 黄銅 (口0.5), 銅下地錫メッキ
PIN: BRASS (口0.5), TIN OVER COPPER PLATING
金具: リン青銅 (±0.25), ニッケル下地錫メッキ
NAIL: PHOSPHOR BRONZE (±0.25), TIN OVER NICKEL PLATING
2. 嵌合相手: 51090, 52484 シリーズ
MATE WITH 51090, 52484 SERIES.
3. 本製品は 55460-***10 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 55460-***10.
4. ELV AND RoHS COMPLIANT.

32.1	33.7	28	34.1	55460-1572	15
28.1	29.7	24	30.1	-1372	13
26.1	27.7	22	28.1	-1272	12
22.1	23.7	18	24.1	-1072	10
18.1	19.7	14	20.1	-0872	8
16.1	17.7	12	18.1	-0772	7
14.1	15.7	10	16.1	-0672	6
12.1	13.7	8	14.1	-0572	5
10.1	11.7	6	12.1	-0472	4
8.1	9.7	4	10.1	-0372	3
6.1	7.7	2	8.1	55460-0272	2
D	C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER No.	極数 CKTS.

CONNECTOR SERIES NO. 55460-***19

REVISED EC NO.: J2013-0327 DRAWN:KMATSUYAMA CHKD:KASAKAWA APPR:YOITO	DESCRIPTION 2012/09/13 2012/09/19 2012/09/20	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
		10 UNDER	±0.2	DRAWN BY DATE T.UENO 2004/03/29		TITLE 2.0 W/B CONN WAFER ASSY FOR SMT ST								
		10 OVER 30 UNDER	±0.25	CHECKED BY DATE M.SASAO 2004/03/29										
		30 OVER	±0.3	APPROVED BY DATE YOITO 2012/09/20		molex								
		ANGULAR ±3 °		MATERIAL NO.							DOCUMENT NO.			SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE							SD-55460-010			1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														

DWG. NO.
SD-55460-011

F

D

V

C

B

DO NOT SCALE DRAWING

8

7

6

5

4

3

2

1

F



E

D


C

B

A




SECT. Y-Y



引き出し方向
PULL OUT DIRECTION


24mm幅キャリアテープ
24mm WIDTH CARRIER TAPE



SECT. X-X


NOTES

- 梱包数量：900個/リール
NUMBER OF CONNECTOR:900PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH



- トップテープの剥離強度：0.1N~1.3N(10gf~130gf) (剥離方向は下図参照)
PEELING OFF FORCE OF TOP TAPE:0.1N~1.3N(10gf~130gf) (PEELING DIRECTION IS SHOWN IN FOLLOWING FIG.)

<剥離速度：300mm/min (参考)>
PEELING SPEED:300mm/min. (REFERENCE)



- 55460-**-19の詳細寸法については図面 SD-55460-010 を参照下さい。
RE DETAILED DIMENSIONS,SEE SD-55460-010

- 材料 (MATERIAL)
キャリアテープ(CARRIER TAPE):ポリプロピレン(POLYPROPYLENE)
トップテープ (TOP TAPE): PET ,PE ,PEF
リール (REEL): ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE(PS)<RECYCLE MATERIAL CONTAINED>
- 本製品は 55460-**-90 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 55460-**-90.

24	29.4	25.4	11.7	16.45	55460-0672	6
			9.7	14.45	55460-0572	5
			7.7	12.45	55460-0472	4
			5.7	10.45	55460-0372	3
			3.7	8.45	55460-0272	2
キャリアテープ幅	D	C	B	A	MATERIAL NO.	種数 CKTS.

55460-**-72	MODEL NO.	DIMENSIONS:	SHT	REV
		☐ mm ☐ INCH ☒ mm ONLY		REVISE ON CAD ONLY

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	TITLE:
DRAWN BY & DATE T.UENO '04/03/29	CHECKED BY & DATE M.SASAO '04/03/29	APPROVED BY & DATE M.SASAO '04/03/29	2.0 W+B Conn WAFER Assy Embstp pkg -LEAD FREE-
CAD FILENAME SD-55460-011.S01	MATERIAL NO.	DRAWING NO.	SHEET NO.
	SEE CHART	SD-55460-011	1 OF 3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			
			SIZE B

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	新規格作成 RELEASED EC NO. J2004-3410 DRWN: T.UENO '04/03/29 CHK: M.SASAO '04/03/29 APPR: M.SASAO '04/03/29
					DESCRIPTION
					REV

MATERIAL 材料	注記参照 SEE NOTES
FINISH 仕上げ	//
WIRE RANGE 適用電線範囲	//
INS. RANGE 被覆外径	//

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	10 UNDER 未満	±0.2
	10 OVER 30 UNDER 以上 未満	±0.25
	30 OVER 以上	±0.3
ANGLE 角度		±3°

8

7

6

5

4

3


2

EN-02J(097) MXJ-54


DWG. NO.

SD-55460-011

DO NOT SCALE DRAWING




SECT. Y-Y




引き出し方向
PULL OUT DIRECTION


32mm幅キャリアテープ
32mm WIDTH CARRIER TAPE



SECT. Y-Y



SECT. X-X



引き出し方向
PULL OUT DIRECTION

44mm幅キャリアテープ
44mm WIDTH CARRIER TAPE

44	49.4	45.4	25.7	30.45	55460-1372	13
			23.7	28.45	55460-1272	12
			19.7	24.45	55460-1072	10
32	37.4	33.4	15.7	20.45	55460-0872	8
			13.7	18.45	55460-0772	7
キャリアテープ幅	D	C	B	A	MATERIAL NO.	極致 CKTS.

EC NO.	DRWN:	CHK:	APPR:	EC NO.	DRWN:	CHK:	APPR:	EC NO.	DRWN:	CHK:	APPR:	EC NO.	DRWN:	CHK:	APPR:	EC NO.	DRWN:	CHK:	APPR:

DESCRIPTION	MATERIAL 材料	SHEET 1 OF 3参照 SEE SHEET 1 OF 3	
	FINISH 仕上げ	//	
	WIRE RANGE 適用電線範囲	//	
REV	INS. RANGE 被覆外径	//	

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	
10 UNDER 未満	±0.2
10 OVER 30 UNDER 以上 未満	±0.25
30 OVER 以上	±0.3
ANGLE 角度	±3°

SCALE --//	DESIGN UNITS ☒ mm ☐ INCH	 THIRD ANGLE PROJECTION	☐ mm INCH	☐ INCH mm	☒ mm ONLY	REVISE ON CAD ONLY
DRAWN BY & DATE T.UENO '04/03/29		TITLE: 2.0 WtB Conn WAFER Assy Embstp pkg -LEAD FREE-				
CHECKED BY & DATE M.SASAO '04/03/29						
APPROVED BY & DATE M.SASAO '04/03/29		MOLEX INCORPORATED				
CAD FILENAME SD-55460-011.S02		MATERIAL NO. SEE CHART	DRAWING NO. SD-55460-011			SHEET NO. 2 OF 3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						SIZE B

DWG. NO.

F

D

V

C

B

DO NOT SCALE DRAWING

8

7

6

5

4

3

2

1

F


E

D


C

B


A



SECT. Y-Y



引き出し方向
PULL OUT DIRECTION
56mm幅キャリアテープ
56mm WIDTH CARRIER TAPE



SECT. X-X

56	61.4	57.4	29.7	34.45	55460-1572	15
キャリアテープ幅	D	C	B	A	MATERIAL NO.	極 数 CKTS.
55460-**-72 MODEL NO.						SHT REV
SCALE: 1:1 DESIGN UNITS: 1mm 1INCH THIRD ANGLE PROJECTION						DIMENSIONS: 1mm 1INCH 1mm ONLY
DRAWN BY & DATE: T.UENO '04/03/29						TITLE: 2.0 WtB Conn WAFER Assy Embstp pkg -LEAD FREE-
CHECKED BY & DATE: M.SASAO '04/03/29						MOLEX INCORPORATED
APPROVED BY & DATE: M.SASAO '04/03/29						MATERIAL NO. DRAWING NO. SHEET NO.
CAD FILENAME: SD-55460-011.S03						SEE CHART SD-55460-011 3 OF 3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.						SIZE B

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:

DESCRIPTION	MATERIAL 材料
FINISH 仕上げ	SHEET 1 OF 3 参照 SEE SHEET 1 OF 3
WIRE RANGE 適用電線範囲	//
INS. RANGE 被覆外径	//

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	10 UNDER 未満	±0.2
	10 OVER 30 UNDER 以上 未満	±0.25
	30 OVER 以上	±0.3
ANGLE 角度		±3°

8

7

6

5

4

3

2

EN-02J(097) MXJ-54