

PRODUCT DATASHEET

LED Project Light
Energizer
INDUSTRIAL

INL2AAE

DEPENDABLE

- Lasts 13 hours between battery changes
- Lifetime pushbutton switch



RUGGED

- Survives a 1-meter drop
- Chemical resistant polypropylene body
- Virtually unbreakable LEDs
- Shatterproof lens



BRIGHT

- Two white Nichia® LEDs provide 13 lumens of light
- Uniform beam profile



HANDY

- Attached woven cloth lanyard
- Convenient hanger hook built into tail cap
- Ribbed grip and non-roll feet



Rugged and dependable, the Energizer® Industrial® LED Project Light is small enough to fit in any toolbox. Or use the handy, built-in carabiner clip to hang it from a tool belt or pipe. This light provides just what the small job needs – bright, consistent light; reliable performance and durability.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Energizer Industrial LED Project Light
Model:	INL2AAE
Color:	Yellow and Black
Power Source:	Two "AA"
ANSI / NEDA:	Series 15
Lamp:	2 White LEDs
Lamp Life (hr):	Lifetime
Lamp Output (lumens):	13
Beam Distance (m):	27
Peak Beam Intensity (cd):	190
Run Time (h:mm):	13
Typical Weight:	72.1 grams without batteries
Dimensions (mm):	41 x 161

Performance:



Tested according to ANSI / NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved