








LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	0	AP2	REVISED	PER ECO-11-004917	11MAR11	RK HMR




- 1 0.000762 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.
- 2 WIRE RANGE: 0.3 – 0.84mm² (24–18 AWG).
- 3 INSULATION RANGE: 2.79 [.110] MAX. DIA.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.



METRIC

GOLD STRIPE	0.25 [.010] BRASS	350417-5
1	0.25 [.010] BRASS	350417-3
PRE-TIN	0.25 [.010] BRASS	350417-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 22NOV2005	 TE Connectivity		
		CHK D. COLEY 22NOV2005			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. COLEY 22NOV2005	NAME	.093 SOCKET COMMERCIAL PIN AND SOCKET —	
	0 PLC ± —	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
	1 PLC ± —	APPLICATION SPEC			
	2 PLC ± —	—	A1	00779	C=350417
	3 PLC ± 0.13 [.005]	WEIGHT			
MATERIAL SEE TABLE		FINISH SEE TABLE	CUSTOMER DRAWING		
			SCALE	5:1	SHEET 1 OF 1
			REV. AP2		