




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

PRODUCT NUMBER
51741-A00CCCDDEF-- NOTE ①
SEE NOTE 1



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	projection	COPY	www.fciconnect.com		title	
H	DG05-0076	SW	04/11/05	linear	.XXX±.005/0.XX±0.13	projection	COPY	product family		PWRBLADE	
J	DG05-0153	SJ	06/09/05	linear	.XXX±.0020/.XX±.051	projection	COPY	size		213	
K	DG05-0479	CS	11/18/05	angles	0°±2°	projection	COPY	dwg no		sheet	
L	DG08-0239	JC	09/11/08	dr	D. EATON 05-25-99	projection	COPY	scale		1 of 3	
				enrg	J. BROWN 05-24-99	projection	COPY	A		51741	
				chr	J. BROWN 05-26-99	projection	COPY	1:1		cage code	
				appd	J. BROWN 05-26-99	projection	COPY	22526		4	
sheet index	revision sheet	L	L	L							
		1	2	3							

Pro/E



PRODUCT NUMBER	DIM	LENGTH FORMULAS (SEE NOTE 10)
51741-A00CCCDDEF-- NOTE ①	DIM "A"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .650 [16.51] (NOTE 10)
SEE NOTE 1	DIM "B"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .350 [8.89]
	DIM "C"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .300 [7.62]
	DIM "D"	.250 [6.35] x DD + .375 [9.53]
	DIM "F"	.250 [6.35] x DD + .100 [2.54] x (CCC/4) + .680 [17.27]
	DIM "G"	.250 [6.35] x DD + .225 [5.72]

CONNECTOR NOTES

- PRODUCT NUMBER CODE:
51741 - A 00 CCC DD E F LF
NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERFACE
ADD THIS SUFFIX: 78u"/2.00um Sn ON PCB INTERFACE
RETENTION TO PCB (NOTE 8)
TAIL OPTIONS (NOTE 7)
NUMBER OF LEFT END POWER CONTACTS (NOTE 6)
NUMBER OF SIGNAL CONTACTS (NOTE 5)
ALWAYS '00' (ZERO, ZERO) (NOTE 4)
PLATING (NOTE 3)
BASE NUMBER
- HOUSING MATERIAL: GLASS FILLED V-O HIGH TEMP THERMO PLASTIC.
SIGNAL CONTACT MATERIAL: COPPER ALLOY
POWER CONTACT MATERIAL: COPPER ALLOY
- PLATING OPTION:
1 = SEE PRINT 10064183 FOR PLATING SPEC OF 51741-100CCCDDEF; 51741-100CCCDDEFLF
- THIS PART NOT AVAILABLE WITH RIGHT SIDE POWER CONTACTS.
- SIGNAL CONTACTS, 004 TO 148 AVAILABLE.
- LEFT END POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR.
- TAIL OPTIONS:
A = .135±.010 [3.43±.25] SOLDER TO BOARD
C = .135±.010 [3.43±.25] PRESS FIT

- RETENTION TO PCB OPTIONS:
A = BOARD LOCK (REQUIRES .098 + .002, -.001
[2.49 +0.05, -0.03] THRU HOLE IN PCB)
BOARD LOCK TO BE USED IN CONJUNCTION WITH
AN .092 PCB OR THICKER.
C = NO RETENTION FEATURE (ALL PRESS FIT).
 - MANUFACTURE'S NAME, P/N, AND DATE CODE
TO APPEAR ON THIS SURFACE.
 - THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART
IS 8.00 [203.2].
 - PRODUCT SPECIFICATION GS-12-149.
 - REFERENCE 51698 FOR SPECIALS WORKSHEET.
- PCB NOTES:
- ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
 - ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION
OF .004 [0.01]
 - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
 - 0.0453±.001 [1.151±.02] DRILLED HOLES PLATED WITH
0.0003 [0.007] MIN SnPb OVER 0.001 [1.03] TO .003 [0.08]
PLATING TO ACHIEVE A .040 ±.003 [1.02 ±.08] HOLE.
 - A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR
NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT
DRAWING REVISION.

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	COPY		projection		title	
L					.XXX±.005/0.XX±0.13					VERTICAL RECEPTACLE W/ GUIDE PIN	
				angles	.XXX±.0020/.XX±.051					SIGNAL / POWER	
				dr	0°±2°					product family	PWRBLADE
				enrg	D. EATON 05-25-99					code	213
				chr	J. BROWN 05-24-99					size	dwg no
				appd	J. BROWN 05-26-99					51741	sheet
					J. BROWN 05-26-99					A	2
sheet index	revision sheet										

Pro/E


cage code 22526

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51741-A00CCCDDEF -- NOTE ①
SEE NOTE 1




SECTION B-B
SCALE 2:1



SECTION C-C
SCALE 2:1



SECTION A-A
SCALE 2:1



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecr no.	dr	date			linear	.XX±.01/0.X±0.3	COPY		projection		title	
L						angles	.XXX±.005/0.XX±0.13					VERTICAL RECEPTACLE W/ GUIDE PIN	
							.XXX±.0020/.XX±.051					SIGNAL / POWER	
						dr	D. EATON 05-25-99					product family	PWRBLADE
						enr	J. BROWN 05-24-99					size	dwg no
						chr	J. BROWN 05-26-99					51741	code
						appd	J. BROWN 05-26-99					3	sheet
sheet index	revision sheet											3	3

Pro/E

cage code 22526