

FrogHide® Ultra Flex® Extension Cords

3-Conductor Grounded • Type SJOW • -40°C to 90°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
06425.63.06	3	14	25	Green	125	15	1875	10	3.0	30	079407064250
06450.63.06	3	14	50	Green	125	15	1875	6	6.0	36	079407064502
06400.63.06	3	14	100	Green	125	13	1625	4	11.4	46	079407064007
06225.61.06	3	12	25	Green	125	15	1875	6	4.3	26	079407062256
06250.61.06	3	12	50	Green	125	15	1875	4	7.9	32	079407062508
06200.61.06	3	12	100	Green	125	15	1875	2	15.9	32	079407062003



Product Description:

Carol® Brand FrogHide® Ultra Flex® extension cords are the most flexible, durable rubber outdoor cords on the market with a name you won't forget. FrogHide cords are molecularly bonded to the caps and connectors with heavy-duty strain reliefs built-in for lasting strength, even in rough applications. Plus, they are resistant to water, oil, ozone and chemicals. FrogHide cords feature an exclusive personal identification system, so you can claim them as your own. They are easy to spot on the job, thanks to the bold, bright green color. FrogHide extension cords come with a limited lifetime warranty.

Product Warranty:

Carol® Brand FrogHide® Ultra Flex® Limited Lifetime Warranty

This product is covered by a limited lifetime warranty against manufacturing defects. If you are not satisfied with this cord, return it with the original packaging to General Cable, 4 Tesseneyer Drive, Highland Heights, KY 41076 for evaluation. This warranty does not cover damage to the cord from long-term use, abuse or from failure to follow electrical codes, laws and regulations relating to building or construction, including Article 305 of the National Electrical Code®. This warranty gives you specific legal rights, and you may also have other rights that vary from state to state.

Product Construction:

Conductor:

- 14 AWG or 12 AWG stranded bare copper per ASTM B-174

Insulation:

- Premium-grade, color-coded 90°C EPDM

Jacket:

- CPE; green
- Temperature range: -40°C to 90°C
- Voltage rating: 300 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- Chain saws
- Wet/dry vacs
- Orbital sanders
- Other outdoor equipment

Features:

- New technology molecularly bonds cap and connector
- Ultra-flexible
- Heavy-duty strain relief
- Personal identification system
- Resistant to water, oil, ozone and chemicals
- Limited lifetime warranty
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable



OSHA Acceptable
Occupational Safety and Health
Administration

