


EDZ 1200



2-24 poles, Spacing 5.08 mm
insert required no. of poles ••
How to order see page 6

Ratings:

*Approvals pending

	 *	 *	 *
	UL1059	CSA 22.2 No. 158	DIN VDE 0627
Rated Voltage	250 VB	300 VB	250 V
Rated Current	15 A	15 A	12 A (T60)
Wire Size	AWG 28-14	AWG 28-14	2.5 mm²
Test Voltage			2.21 kV
Rated Torque/Screw Size			0.5 Nm/M2.5

Rated Cross Section



Single Wire (solid)	2.5 mm ²
Stranded Wire (flexible)	2.5 mm ²
Stranded wire with Ferrules	2.5 mm ²

Dimensions

Spacing	5.08 mm
Stripped Length	10.0 mm

Materials

Insulating Material	PA
Flammability Class	UL94 V-0
Temperature Range	-30°C/+105°C
Clamp Cage	Fe/Fe
Contact	CuSn
Color	Green



P = No. of Poles