

6 outlet, 6-ft cord, 1340 joule, Metal strip - Protect It! Surge Suppressor

MODEL NUMBER: **TLM606HJ**



Highlights

- 6 outlets / 6 ft. cord
- 1340 joule rating
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for personal computers, TV/VCR/DVD, stereos, power tools and lamps/lighting

Package Includes

- TLM606HJ surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's TLM606HJ surge suppressor offers complete AC surge suppression for comprehensive protection of personal computers, home stereos, televisions, VCRs, DVD players, power tools and other electrical and electronic equipment. Heavy-duty AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLM606HJ offers 6 total outlets, a 6 foot power cord and diagnostic LED to warn of suppressor damage. AC surge suppression rated at 1340 joules shields equipment from surges and line noise. Rugged metal housing offers convenient protection of desktop computer equipment and accessories. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input - 6 ft. AC line cord with NEMA 5-15P plug/Output - 6 NEMA 5-15R outlets

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

FORMAT: Metal strip

SUPPRESSION: AC: 150V RMS Clamping/1340 joules/400V UL1449 3rd Edition

Features

- 6 outlets
- 6 ft. cord
- Surge suppression rating: 1340 joules
- EMI/RFI noise filtering
- Diagnostic LED confirms suppressor "protection present" (green)
- Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 1 transformers without blocking adjacent outlets
- Rugged metal case provides extra safety and durability
- Illuminated on/off switch with integrated 15 amp circuit breaker
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment

Specifications

OVERVIEW

Intended Application	Home/Office
Style	Strip

OUTPUT

Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Circuit Breaker (amps)	15
Outlet Quantity / Type	6 NEMA 5-15R
Number of Outlets	6
Transformer Accommodation	Supports 1 large transformer without covering adjacent outlets
Outlet Orientation	Single row of outlets

INPUT

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000

LEDS ALARMS & SWITCHES

Switches	Illuminated on/off switch with integrated 15 amp circuit breaker
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status

SURGE / NOISE SUPPRESSION

AC Suppression Joule Rating	1340
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20dB

DATALINE SURGE SUPPRESSION

Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	1.75 x 15.5 x 4.5
Shipping Dimensions (hwd / cm)	4.4 x 39.4 x 11.4
Shipping Weight (lbs.)	1.6
Shipping Weight (kg)	.7
Unit Dimensions (hwd / in.)	1.5 x 12.5 x 2.5
Unit Dimensions (hwd / cm)	3.8 x 31.8 x 6.3
Unit Weight (lbs.)	1.4
Unit Weight (kg)	.6
Material of Construction	Metal top enclosure, plastic bottom insert
Integrated Keyhole Mounting Tabs	Keyhole slots enable mounting to a variety of surfaces
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Form Factors Supported	Supports floor / wall / desktop placement
Outlets Measurement (Center to Center)	38.89mm
CERTIFICATIONS	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance