


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 241307



P/N	MFG	Resistance (Ohms)	Characteristics			
241235	3006P-1-101	100	Total Mechanical Travel	22±2 cycles	Starting Torque	30mN.m
241294	3006P-1-103	10,000				
241332	3006P-1-104	100,000	Withstand Voltage	101.3KPa 600V 8.5KPa 350V	Terminal Resistance	≤2G Ω
241374	3006P-1-105	1,000,000				
241307	3006P-1-203	20,000	Effective Electrical Travel	22±2 cycles	Standard Packaging	25pcs/tube
241350	3006P-1-204	200,000				
241252	3006P-1-501	500	Rated Power	+70℃ 0.75W +125℃ 0W	Mechanical Endurance	200 cycles △R≤±3%
241286	3006P-1-502	5,000				
241323	3006P-1-503	50,000	Insulation Resistance	R _i ≥1G Ω	Temperature Range	-55℃ ~+125℃