


REV.	DATE	DESCRIPTION
A	05/01/04	UPDATE DRAWING FORMAT
B	10/10/07	REMOVE CRIMP NOTES



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex							
8						DRAWN	G.R.S.							10/10/07	
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	CHECKED			PART DESCRIPTION						
6					0.5 – 8mm ± 0.20mm	ISSUED									
5					8 – 30mm ± 0.40mm				SMA PANEL RECEPT. JACK						
4					30 – 120mm ± 0.50mm										
3	CONTACT PIN	BER. COPPER	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	SHEET	1 OF 1		PART NO.						
2	INSULATOR	TEFLON	NATURAL	1	.020 – .315 = ± 0.007"										
1	BODY	BRASS	GOLD	1	.315 – 1.180 = ± 0.015"				132204						
					1.180 – 4.724 = ± 0.020"										
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/132/132204.DWG	DWG. NO.	132204.DWG	REV.	B	SIZE	A	SCALE	NA