




NOTES:
1.MATERIAL:
HOOD:THERMALPLATIC UL94V0;
BODY:GLASSFIBER REINFORCED THERMALPLASTIC UL94V0;
CONTACTS:PHOSPHOR BRONZE;
PLATING:GOLD OVER 2um NICKEL ON WORKING AREA.
2.MECHANICAL REQUIREMENT:
INSERTION FORCE(EACH CONTACT):<=1N;
WITHDRAWAL FORCE (EACH CONTACT):>=0.19N;
DURABILITY:>=100CYCLES.
3.ELECTRICAL REQUIREMENT:
INITIAL CONTACT RESISTANCE:<=20MILLIOHM;
INSULATION RESISTANCE AFTER TEST:>=10000MEGAOHM;
WITHSTANDING VOLTAGE:>1000Vrms;
OPERATING VOLTAGE:250VAC;
OPERATING CURRENT:1.3A AT 70 DEGREE.
4.IF LEAD FREE P/N, GS-14-920 SHOULD BE APPLIED.
5.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



PLATING CODE&GOLD THICKNESS		E9 Au:1u		Z4 or Z6 Au:0.8u			
PART NUMBER							
5							
HPTE1597							PLASTIC CABLE CLAMP
HPTE1586							CABLE CLAMP #7.2
4							CABLE CLAMP #12.5
HPTE1585/A							CROSSHEEDED SCREW
HPTE1585							OR SLOTTED SCREW
3							CABLE HOOD
BPBS1B06P4							
2							
BPCD3P2---(LF)							CONTACT FOR AWG24(IDENTIFICATION-3)
BPCD2P2---(LF)							CONTACT FOR AWG26(IDENTIFICATION-2)
BPCD0P2---(LF)							CONTACT FOR AWG30(IDENTIFICATION-0)
1							
BPBS1B06P9							BODY FOR AWG30(COLOR=WHITE)
BPBS1B06P8							BODY FOR AWG26(COLOR=BLACK)
BPBS1B06P1							BODY FOR AWG24(COLOR=GREY)
ITEM CATALOG N°		QTY. FOR COMPLETE ASS'Y		DESCRIPTION		DRAWING	

mat'l. code 14				tolerances unless otherwise specified				CUSTOMER COPY		A FCI www.fciconnect.com					
ltr	ecn no	dr	date	linear	.X ± 0.5				projection	title ASSY 2X3 CAPOT & CON. VXX27633					
A	F03021	DLE	01/29/03		.XX ± 0.30										
B	N05-0223	AILEI	09/05/05												
				angles	± 2°					product family DIN size dwg no A4 VJW12163					
				dr	D LEGRAND	01/29/03	MM								
				engr	F TISSERAND	01/29/03	← MM →								
				chr	JF NOTTTEAU	01/29/03	scale 1:1								
				appd	F. TI	01/29/03			sheet 1 of 1						
sheet index		revision		B											
		sheet		1											