



Home > ... > [M12™ Cordless LITHIUM-ION System](#) > [M12™ Cordless LITHIUM-ION 3/8" Drill Driver](#)

M12™ Cordless LITHIUM-ION 3/8" Drill Driver 2410-22



4.7 [Read 6 Reviews](#) [Write a Review](#)

The M12™ Cordless LITHIUM-ION 3/8" drill driver delivers 275 in-lbs of torque in a compact light weight design. The only tool in its class with an all metal locking chuck, the 2410-22 drills and fastens up to 35% faster than the competition. The on board fuel gauge displays remaining run-time, while a built in L.E.D. illuminates work surface.

Includes

- 2410 M12™ Cordless LITHIUM-ION 3/8" Drill Driver
- (2) M12™ RED LITHIUM™ Batteries
- 30 Minute Charger
- Carrying Case

FEATURES

- 2-Speed (0-1,500/0-400) All Metal Gear Box--Up to 35% faster drilling / fastening and Milwaukee durability
- Powerful Motor: Delivers 275 in-lbs. of torque-- Up to 25% More Torque
- 3/8" Single Sleeve ratcheting metal chuck--Increased bit retention and durability
- Lightweight and Compact--Tool belt portable at only 2.5 lbs. and 7-3/8"
- Integrated LED and Fuel Gauge-- Increased productivity and decreased frustration.

SPECIFICATIONS

Voltage	12V
Speed	2 Speed
No Load Speed	0-400/0-1,500 RPM
Torque	275 in-lbs
Chuck Type	3/8 in
Single Sleeve	Yes
Metal Sleeve	Yes
Ratcheting Lock	Yes
On Board Fuel Guage	Yes
LED Light	Yes
Battery	M12™ RED LITHIUM™
Length	7-3/8"
On-Board Bit Storage	No
Tool Weight (w/battery)	2.5 lbs
Shipping Weight	7.18 lbs
No of Batteries Included	(2) M12™ REDLITHIUM™ Batteries
Charge Time	30 minutes

RELATED ARTICLES

- Milwaukee M12 Drill Driver (2410-22) Review
- Milwaukee 2410-22 Wins Popular Woodworking
- Milwaukee Wins Popular Mechanics "Best Overall"