





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		L4	WIRE SIZE CORRECTION	05MAR2015	CR	PS

MATERIALS:
HOUSING: POLYAMIDE, UL94V-0
TERMINALS: COPPER ALLOY, TIN PLATED
SCREWS: STEEL, ZINC PLATED, EXCEPT WHERE NOTED.


ELECTRICAL:
RATING: 20A, 150V(300V LIMITED RATING)
UL & CSA.

MECHANICAL:
WIRE RANGE: 12 AWG - 22 AWG
MAXIMUM TIGHTENING TORQUE: 7 IN-LBS.


- 1
- SCREWS ARE ALL BOTTOMED, NO RUNNING TORQUE.
- 2
- PERMANENT WHITE LETTERING.
- 3
- SCREWS ARE NICKEL PLATED BRASS.
- 4
- PRELIMINARY PART NUMBER.
- 5
- PCB RETENTION FEATURE.
- 6
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



2-796607-1



4-1437649-0



RECOMMENDED HOLE LAYOUT
TOLERANCE ±.002, UNLESS OTHERWISE SPECIFIED

		9.425	30	4PCV-30-006	1-1546158-3	
		9.100	29	4PCV-29-006	1-796607-5	
		8.775	28	4PCV-28-006	1-796607-4	
		8.450	27	4PCV-27-006	1-1546158-2	
		8.125	26	4PCV-26-006	1-796607-3	
		7.800	25	4PCV-25-006	1-1546158-1	
△	OBSOLETE	7.475	24	4PCV-24-501	4-1437649-0	
		7.475	24	4PCV-24-006	3-1437649-9	
		7.150	23	4PCV-23-006	1-1546158-	
		6.825	22	4PCV-22-006	3-1437649-6	
		6.500	21	4PCV-21-006	1-796607-2	
		6.175	20	4PCV-20-006	3-1437649-4	
		5.850	19	4PCV-19-006	1546158-9	
		5.525	18	4PCV-18-006	2-1437649-9	
		5.200	17	4PCV-17-006	2-1437649-7	
		4.875	16	4PCV-16-006	2-1437649-5	
		4.550	15	4PCV-15-006	1546158-6	
		4.225	14	4PCV-14-006	2-1437649-0	
		3.900	13	4PCV-13-006	1-1437649-7	
		3.575	12	4PCV-12-006	1-1437649-5	
△	OBSOLETE	3.250	11	4PCV-11-525	2-796607-2	
		△5△4	11	4PCV-11-524	2-796607-1	
		3.250	11	4PCV-11-006	1-1437649-2	
△	OBSOLETE	2.925	10	4PCV-10-392	1-1546119-1	
		2.925	10	4PCV-10-006	1437649-5	
		2.600	9	4PCV-09-006	1437649-1	
△3	OBSOLETE	2.275	8	4PCV-08-495	9-1437648-7	
		2.275	8	4PCV-08-006	9-1437648-1	
		△4△3	7	4PCV-07-524	2-796607-0	
		1.950	7	4PCV-07-006	8-1437648-6	
		△4△3	6	4PCV-06-523	1-796607-9	
	OBSOLETE	1.625	6	4PCV-06-513	796607-9	
		△3	6	4PCV-06-391	3-1437650-2	
		1.625	6	4PCV-06-006	8-1437648-0	
△	OBSOLETE	1.300	5	4PCV-05-520	1-796607-6	
		△3	5	4PCV-05-397	796607-1	
		1.300	5	4PCV-05-006	7-1437648-4	
		△4△3	.975	4	4PCV-04-522	1-796607-8
	OBSOLETE	.975	4	4PCV-04-512	796607-8	
		.975	4	4PCV-04-006	6-1437648-7	
		△4△3	.650	3	4PCV-03-521	1-796607-7
		.650	3	4PCV-03-515	1-796607-1	
		.650	3	4PCV-03-006	6-1437648-1	
		.325	2	4PCV-02-514	1-796607-0	
	OBSOLETE	.325	2	4PCV-02-511	796607-7	
		.325	2	4PCV-02-006	5-1437648-7	
		DIM. "A"	NO. OF POS.	CATALOG NUMBER	TE PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL		27JUN02		 TE Connectivity					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK S. YODER 7/9/02		NAME 4PCV-XX-006 ASSEMBLY					
		APVD S. YODER 7/9/02		PRODUCT SPEC —							
		APPLICATION SPEC —		SIZE A2							
		WEIGHT —		CAGE CODE 00779							
MATERIAL —		FINISH —		CUSTOMER DRAWING		DRAWING NO C=5-1437648-7		RESTRICTED TO —			
						SCALE NTS		SHEET 1 of 1		REV L4	