

VIDEO LIBRARY[Video Library](#)**SEARCH**

By Type of User:

By Type of Application:

By Keyword:

TO PURCHASE[Request A Quote](#)[USA Distribution](#)[International Distributors](#)[Sales Representatives](#)[Becoming a Distributor](#)[Contact Us](#)**DOWNLOADS**[Catalog](#)**Products**[Products](#) > [All Station](#) > [V36GL3](#)**60 Watt Industrial Grade Soldering Station****Model:** V36GL3**Standard Tips:**

- 704 - Paragon Soldering Iron Tips
- 709 - Paragon Soldering Tips
- 724 - Paragon Soldering Iron Tips

**Applications:**

- Soldering stained glass for finer detailed soldering
- Soldering conductor of neon light bulb to create hermetic seal

Specifications:

- 1/4" Chisel, Diamond and Conical Style Soldering Tips
- Max Tip Temperature of 1,100°F
- Working Temperature Range of 225°F to 1,100°F

Weight: 1.0 Lbs. (0.45 Kgs)**Diameter:** 1/4[+ Add to Quote](#) - [Product Link](#)**American Beauty Soldering Tools are proudly manufactured by Assembly Technologies International, Inc.**

1177 West Maple Road Clawson, MI 48017-1059 United States -- Phone: 800-550-2510

Copyright © 2000 - 2010 :: American Beauty Tools