



Heyco®-Tite Brass Liquid Tight Cordgrips


PG Hubs

The Ultimate in Liquid Tight Strain Relief Protection

- Nickel plated brass construction for superior protection of flexible cables.
- Nickel-plated finish over brass provides excellent corrosion resistance and durability.
- IP 68 rated.
- For use in clearance or threaded holes.
- Long PG threads provide additional threads for easy locknut assembly.
- Multiple sizes for flexible cord diameters ranging from .138" (3,5 mm) to 1.654" (42,0 mm).
- We recommend using the smallest cordgrip that accommodates your cable size.
- Sealing gland is molded in Thermoplastic Polymer Elastomer (TPE) Material.
- **Locknuts not included.**
For metal locknut specifications or to order locknuts separately, see page 3-40.

CABLE DIA. RANGE				PART NO.	THREAD SIZE	UL or CSA	PART DIMENSIONS				D Wrenching Nut Flat Size				
Minimum		Maximum					A Clearance Hole Dia.		B Max. O.A. Length		C Thread Length				
in.	mm.	in.	mm.				in.	mm.	in.	mm.	in.	mm.			
.138	3,5	.197	5,0	4530											
.197	5,0	.256	6,5	4531	PG 7	c CSA us	.500	12,7	1.063	27,0	.394	10,0			
.256	6,5	.315	8,0	4532											
.256	6,5	.295	7,5	4611*	PG 7	c CSA us	.500	12,7	.906	23,0	.236	6,0			
.138	3,5	.177	4,5	4533											
.177	4,5	.236	6,0	4534											
.236	6,0	.315	8,0	4535	PG 9	c CSA us	.610	15,5	1.181	30,0	.394	10,0			
.315	8,0	.413	10,5	4536											
.157	4,0	.216	5,5	4537											
.216	5,5	.335	8,5	4538	PG 11	c CSA us	.748	19,0	1.220	31,0	.394	10,0			
.335	8,5	.472	12,0	4539											
.236	6,0	.315	8,0	4540											
.315	8,0	.433	11,0	4541	PG 13.5	c CSA us	.827	21,0	1.220	31,0	.394	10,0			
.433	11,0	.590	15,0	4542											
.236	6,0	.315	8,0	4543											
.315	8,0	.433	11,0	4544	PG 16	c CSA us	.906	23,0	1.220	31,0	.394	10,0			
.433	11,0	.590	15,0	4545											
.374	9,5	.492	12,5	4546											
.492	12,5	.630	16,0	4547	PG 21	c CSA us	1.142	29,0	1.457	37,0	.472	12,0			
.630	16,0	.807	20,5	4548											
.630	16,0	.748	19,0	4549											
.748	19,0	.905	23,0	4550	PG 29	c CSA us	1.476	37,5	1.575	40,0	.472	12,0			
.905	23,0	1.083	27,5	4551											
.846	21,5	1.024	26,0	4552											
1.024	26,0	1.201	30,5	4553	PG 36	c CSA us	1.858	47,2	1.850	47,0	.591	15,0			
1.201	30,5	1.378	35,0	4554											
1.142	29,0	1.299	33,0	4555											
1.299	33,0	1.457	37,0	4556	PG 42	c CSA us	2.138	54,3	1.929	49,0	.591	15,0			
1.457	37,0	1.654	42,0	4557											

*Short .236" (6,0 mm) thread



**Quick
Specs**

Material	Nickel-Plated Brass w/TPE Sealing Gland
Certifications	Certified by UL for Compliance with both Canadian and U.S. requirements under File E51579.
	Recognized under the Component Program of Underwriters' Laboratories File E51579 to both Canadian and U.S. requirements.
Temperature Rating	-40°F (-40°C) to 212°F (100°C)
IP Rating	IP 68, IP 69K

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[4545](#) [4535](#) [4536](#) [4542](#) [4551](#) [4534](#) [4531](#) [4539](#)