


T3/DS3/E3/STS-1 TRANSFORMERS

Twelve Transformers Designed for T3, DS3, E3 and STS-1 Interface



- ⦿ Twelve transformers in a surface mount package
- ⦿ Extended temperature range of -40°C to +85°C
- ⦿ Return loss meets requirements of G.703
- ⦿ Recognized by UL1950 (pending)
- ⦿ Isolation voltage: 1500 Vrms


Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Turns Ratio (Pri:Sec ±2%)	OCL Primary @ 25°C (μH MIN)	OCL Primary @ -40°C (μH MIN)	LL (μH MAX)	C _{ww} (pF MAX)	Isolation Voltage (Vrms MIN)	Primary Pins
TX3051	1:1	60	40	.120	12	1500	1-2, 3-4, 5-6, 7-8 9-10, 11-12, 13-14, 15-16 17-18, 19-20, 21-22, 23-24
TX3052	1:2	40	19	.110	12	1500	1-2, 3-4, 5-6, 7-8 9-10, 11-12, 13-14, 15-16 17-18, 19-20, 21-22, 23-24


Note: Crosstalk is typically -60 dB.

Mechanical

TX3051/TX3052



Schematic



Tape & Reel250/reel
Tube15/tube

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified,
all tolerances are $\pm \frac{.010}{0.25}$

For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
<http://www.pulseeng.com>
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be products and/or registered trademarks of their respective owners.