




Twist-Lock® Devices

20 Ampere, 347, 480 and 600 Volts AC

2 Pole, 3 Wire Grounding

**Insulgrip® Plugs, Flanged Inlets,
Connector Bodies and Receptacles****HBL2341****HBL2345****HBL2343****HBL2340****HBL2346****IP20**
SUITABILITY**20A 347V AC**
NEMA L24-20P
UL/CSA**20A 480V AC**
NEMA L8-20P
UL/CSA
3 HP**20A 600V AC**
NEMA L9-20P
UL/CSA**Plugs**

Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.360"-.930" (9-24)	HBL3721	HBL2341	HBL2351

Accessories on page B-51.

Flanged Inlets

Description	Catalog Numbers		
Nylon casing, back wired.	HBL3725	HBL2345	HBL2355

Accessories on page B-50.

IP20
SUITABILITY**20A 347V AC**
NEMA L24-20R
UL/CSA**20A 480V AC**
NEMA L8-20R
UL/CSA
3 HP**20A 600V AC**
NEMA L9-20R
UL/CSA**Connector Bodies**

Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.360"-.930" (9-24)	HBL3723	HBL2343	HBL2353

Accessories on page B-51.

Single Flush Receptacles, Back and Side Wired

Description	Catalog Numbers		
Black nylon face.	HBL3720	HBL2340	HBL2350
Isolated ground, orange nylon face.	-	IG2340	-

Accessories on page B-50.

Flanged Receptacles

Description	Catalog Numbers		
Nylon casing, back wired.	HBL3726	HBL2346	HBL2356

Accessories on page B-50.

Notes: Only receptacles and plugs up to 480V AC are HP rated.

For technical information see page B-69.

See page B-37 for switched enclosure.

See page B-40 for Add-A-Shroud™ kit. For use with connector bodies.

HP ratings are AC only.