


Sockets

KD 10



Product	KD 10		
description	Insulated coupling with a nickel-plated brass tube for two 4 mm diameter plugs.		
operating instruction	BA407		
article-no. / *colour	9301091xx  00 black  01 red Ni		
drawing			
technical data			
connection	unsprung socket 4 mm		
rated voltage ⁽¹⁾	30 VAC / 60 VDC		
measurement cat. acc. to IEC 61010	O ⁽³⁾		
rated current ⁽¹⁾ (consider derating curve)	10 A		
material socket	brass, nickel plated		
housing material	PS		
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +70 °C		
standard	IEC 61010		

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 17.09.2018