



T&B® Fittings

PRINT

Rigid/IMC Conduit Fittings

T&B Catalog Number: 370
UPC Number: 78621000370
Status: Active

Description:
1/2" Hub Connector, Steel-Electro Zinc Plated, Nylon Insulated. For use with Rigid/IMC Conduit.

ROHS CAD SUBMITTAL PACKAGE

Where To Buy

Enter Zip Code:
Enter Quantity:

Features

- Rugged steel/malleable iron construction
- Tapered internal threads for water-tight/dust-tight union
- Threads relieved to prevent bottoming of conduit, ensuring sound assembly
- Recessed sealing ring at box end; sealing ring captivated
- Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures
- Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort

General

Material Steel
Finish Electro Zinc Plated

Dimension Information

Hub Size (inches) 1/2
Dimension A (inches) 1 3/8
Dimension B (inches) 1 1/4
Dimension C (inches) 1/2

Packaging

Inner Package 25
Outer Package 100
Package Height 6.3
Package Length 9.6
Package Width 8.6
T&B Sold in UOM Each
T&B Weight Per UOM 17.6 lbs. per 100

Application Support

 Spacing Chart [Click Here](#)

Notes

*Note Available with DURA-PLATEO Finish

Certifications

RoHS Compliance Yes [Generate Compliance Certificate](#)

Certifications



File Nbr:
E 23018

HOME
Global Site
Report Issue

LOGIN
T&B Access (Dist only)
Suppliers
MyTNB

RESOURCES
Catalog PDFs
End User Toolkit
Solution Set Brochures
Vertical Market Brochures
Where To Buy

SUPPORT
Contact Us
Global Locations
Product Support
Tool Services
Terms

COMPANY
About Us
Careers
Employees
News

Thomas & Betts®
© 2012 Thomas & Betts Corporation
No material from this site may be copied, distributed or in any way used without the expressed prior permission of Thomas & Betts.