


MALE END VIEW

1
3
4

SPECIFICATIONS	
HOUSING MATERIAL/COLOR	NYLON/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	75 VDC/60 VAC
MAXIMUM WIRE SIZE	22 AWG
CABLE GRIP RANGE	3-5mm
TEMPERATURE RANGE	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67
CONDUCTOR TERMINATION	SCREW TERMINALS



SOURCE DRAWING - FOR REFERENCE ONLY

NOTE: 0.9 MM HEX KEY TOOL PROVIDED

B	ADDED EXPLODED VIEW	RWC	06/10/05	13222
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS	1.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com			
	2.						
	3.						
	4.						
MATERIAL	SEE SPECIFICATIONS	DRFT	JB	DATE	11/06/00	DESCRIPTION	BS 5133-0
FINISH	SEE SPECIFICATIONS	DSGN		SCALE	1=.5		
		UNIT OF MEASUREMENT		MILLIMETERS		IDENTIFICATION NO.	REV
		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		U6512	B
						FILE: U6512	SHEET 1 OF 1