



Heyco® Liquid Tight Threaded Plugs

Liquid Tight with Integral Sealing Ring

THREAD TYPE/SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS			
	Black	Gray		A Wrenching Flats		B Overall Length	
				in.	mm.	in.	mm.
NPT							
NPT 1/4	3544B	3544	LTPP NPT 1/4	.63	16,0	.66	16,8
NPT 3/8	3545B	3545	LTPP NPT 3/8	.83	21,1	.69	17,5
NPT 1/2	3546B	3546	LTPP NPT 1/2	.98	24,9	.81	20,6
NPT 3/4	3547B	3547	LTPP NPT 3/4	1.29	32,8	.86	21,8
NPT 1	3548B	3548	LTPP NPT 1	1.74	44,2	1.05	26,7
NPT 1-1/4	3549B	3549	LTPP NPT 1-1/4	2.06	52,3	1.08	27,4
PG*							
PG 7	3574B	3574	LTPP PG 7	.63	16,0	.53	13,5
PG 9	3575B	3575	LTPP PG 9	.83	21,1	.53	13,5
PG 13.5	3576B	3576	LTPP PG 13.5	.98	24,9	.62	15,8
PG 21	3401B	3401	LTPP PG 21	1.29	32,8	.68	17,3
PG 29	3578B	3578	LTPP PG 29	1.74	44,2	.87	22,1
PG 36	3579B	3579	LTPP PG 36	2.06	52,3	.78	19,8
Metric							
M12	3582B	3582	LTPP M12	.63	16,0	.53	13,5
M16	3583B	3583	LTPP M16	.83	21,1	.53	13,5
M20	3584B	3584	LTPP M20	.98	24,9	.62	15,8
M25	3585B	3585	LTPP M25	1.29	32,8	.76	19,3
M32	3586B	3586	LTPP M32	1.74	44,2	.87	22,1
M40	3587B	3587	LTPP M40	2.06	52,3	.78	19,8

Standard color black. Consult Heyco for other colors.

*For PG Thread Specifications, see page 3-37.

- Integral sealing ring ensures a superior seal at mounting hole location, every time.
- IP 68 Rated.
- Provide a liquid-tight seal up to 70 psi.
- Threaded plugs for hydraulic and pneumatic applications.
- Seal threaded openings and protect against contamination and moisture.
- Lower cost option over brass or steel NPT and PG plugs.
- Non-corrosive—resist salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents.
- Resist oil and heat up to 221°F (105°C).
- Approximate Head Thickness: .21" (5,3 mm). Thickness may vary.
- Hex shaped head with slot for wrench or screwdriver installation.
- Electrically non-conductive Nylon 6/6.



NEW!

NEW!

NEW!

NEW!

NEW!



INTEGRAL SEALING RING

Material: Nylon 6/6
 Flammability Rating: 94V-2
 Material Temperature Index: 257°F (125°C) - Maximum Temperature on part not to exceed 221°F (105°C)
 IP Rating: IP 68 (70 PSI, 5 BAR)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3546](#) [3547B](#) [3584B](#)