



English | 简体中文 | 日本語

Search Entire Site [GO](#)

[Contact IDT](#) | [Investors](#) | [Press](#)

[About IDT](#)

[Products](#)

[Applications](#)

[Support](#)

[myIDT](#)

[Document Search](#) | [Package Search](#) | [Parametric Search](#) | [Cross Reference Search](#) | [Green & RoHS](#) | [Calculators](#) | [Thermal Data](#) | [Reliability & Quality](#) | [Military](#)

[Home](#) > [Products](#) > > [950902](#) > [950902DGLF](#)

[Add to myIDT \[?\]](#)

You may also like...

## 950902DGLF

Category:

Generic Part:

Market Group:

Description:

950902

PC CLOCK

PC MAIN CLOCK

**Time is  
money**

### Parameters

|                         |                  |
|-------------------------|------------------|
| Package                 | TSSOP 56 (PAG56) |
| Speed                   | NA               |
| Temperature             | C                |
| Voltage                 | 3.3 V            |
| Status                  | Active           |
| Sample                  | Yes              |
| Minimum Order Quantity  | 68               |
| Factory Order Increment | 34               |

### Distributor Inventory

No Pricing information is available from our Distributors at this time.

### Documents

| Type | Title                  | Size  | Revision Date |
|------|------------------------|-------|---------------|
| Misc | PC Clocks Contact Info | 61 KB | 05/29/2007    |

### Package

|                                  |                          |
|----------------------------------|--------------------------|
| Description                      | TSSOP 6.10 MM            |
| Class                            | PLASTIC                  |
| Moisture Sensitivity Level (MSL) | 1                        |
| Category                         | Green                    |
| Moisture Exposure Floor Life     | Unlimited @ <30°C/85% RH |
| Peak Reflow Temperature          | 260°C                    |
| Rebake Conditions                | N/A                      |
| Length                           | 14.0                     |
| Mark                             | G                        |
| Width                            | 6.1                      |
| Pitch                            | 0.5                      |
| Thickness                        | 1.0                      |
| Status                           | Active                   |

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. **All Rights Reserved.**