


THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	20A 125V AC, 16A 250V AC		Mounting Hole 	Circuit Diagram  SPST ON - OFF
Contact Resistance	50m ohm max.			
Insulation Resistance	DC 500V 100M ohm min.			
Dielectric Strength	AC 1500V 1 minute			
Operating Temperature	-25°C ~ 85°C			
Switch Function	2P SPST ON - OFF			





MATERIAL:

Frame: Nylon 66 (94 v-2), Black

Actuator: Nylon 66 (94 v-2), Black

Terminals: Silver plated Copper alloy.

Printed: White, Hot stamping



RoHS Compliant

1 Revised 7/14/2010 - Added I O to button.



INDUSTRIES
Southampton, Pa. 18966

Tel 215.355.7080/www.cwind.com

Date Drawn: 12/21/09

Rev. 1

Unit: mm

Checked
By:

G.Guld

Title:

ROCKER SWITCH

CW P/N:

GRB293A01BB