



10A / 15A / 25A / 35A SINGLE - PHASE SILICON BRIDGE

- Surge overload 200 - 400 Amperes peak
- Low forward voltage drop
- Mounting Position: Any
- Electrically isolated base-180 Volts
- Solderable .25" FASTON terminals
- Materials used carries U/L recognition

LEAD / METAL




LEAD / PLASTIC



Rating at 25 °C ambient temperature unless otherwise specified. Resistive or inductive load 60Hz
For capacitive load current by 20%.

[illegible]

NOTE: Also available on KBPC 10W/15W/25W/35W series.



(wholly owned subsidiary of **HONEY TECHNOLOGY LTD.**)



KBPC10, 15, 25, 35 ...
10A / 15A / 25A / 35A SINGLE - PHASE SILICON BRIDGE

RATING AND CHARACTERISTICS CURVES
KBPC10/15/25/35 SERIES

FIG. 1-MAXIMUM FORWARD SURGE CURRENT




FIG. 2-DERATING CURVE FOR
OUTPUT RECTIFIED CURRENT




FIG. 3-TYPICAL FORWARD
CHARACTERISTICS




FIG. 4-TYPICAL REVERSE
CHARACTERISTICS

