


SWITCHES **ROCKER**

LIGHTED HEAVY DUTY ROCKER SWITCHES

SPECIFICATIONS:

Current Rating:	15A @ 125V AC, 10A @ 250 VAC 1/2HP 125-250VAC				
Insulation Resistance:	100 Meg ohms. (Min.)				
Dielectric Strength:	1000V (Min.)				
Base Material:	Phenolic				
Terminal Type:	.250" Quick Connect				
Part No.	Type	Action			Actuator
30-652	SPST	ON	-	OFF	Amber Nylon

* Lamp Voltage 125VAC/Neon




Mounting Hole: 0.83" x 1.45"



SPECIFICATIONS:

Current Rating:	20A @ 125V AC, 15A @ 250 VAC 16 (6) A-125VAC T85, 125A Peak Inrush Current				
Insulation Resistance:	100 Meg ohms. (Min.)				
Dielectric Strength:	1000V (Min.)				
Base Material:	Nylon				
Actuator Material:	Nylon/Polycarbonate				
Terminal Type:	.250" Quick Connect				
Part No.	Type	Action			Actuator
30-16867	DPST	ON	-	OFF	Red Translucent

LIGHTED HIGH INRUSH HEAVY DUTY ROCKER SWITCH






Mounting Hole: 0.872" x 1.125"



SPECIFICATIONS:

Current Rating:	10A @ 125VAC, 6A @ 250VAC				
Initial Contact Resistance:	50 Meg ohm (Max.)				
Insulation Resistance:	DC 300V 100 Meg ohm. (Min.)				
Dielectric Strength:	1500VAC for 1 Min.				
Terminal Type:	.187" Quick Connect				
Part No.	Type		Action		Actuator
30-16086	SPST	ON	-	OFF	Red Nylon


* Lamp Voltage 125VAC/Neon 33K ohm



Mounting Hole: 0.512" x 0.756"



CIRCUIT DIAGRAM



Lamp Voltage: Neon 105-125V AC

SPECIFICATIONS:

ELECTRICAL RATINGS:					
20A	125-250V AC 85C				UL E45221
1/2HP	125V AC 1HP 250V AC				UL E45221
20A	125-250V AC				CSA LR10990
16 (4)A	250V AC T85				VDE 62411
150A	Inrush				Semko IEC 65
Part No.	Type	Action			Actuator
30-866	DPST	ON	-	OFF	Black Plastic w/ Red Neon
30-867	DPST	ON	-	OFF	Red Plastic



LIGHTED ROCKER SWITCHES

