

[Request more info](#)**Part Number : 5219488F**

5219488F



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	521
Configuration	3 mm Lens
Description	Discrete LED Lamp
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Color
Lens Color	Non-Tinted, Diffused

Absolute Maximum Ratings (Ta = 25°)

Solder Temperature	260° for 6 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics

Standard Efficiency	Green 
Luminous Intensity Min	3.7
Luminous Intensity Typical	10
Test Current mA	20mA
Power Dissipation Max	100mW

Red 
2.5
4.7
20mA

[Share](#) |