


4 Position Dimmer for LED Light Panels from Inspired LED

Specifications:	
Supply Voltage: DC 12VDC	Size: (L) 58 x (W) 36 x (H) 10 mm
Max load current: 2 Amp	Net Weight: 15g
Output: 1 channel	Working Temperature -20- 60°C
Static power consumption: < 1 Watt	
Output Power: 24 Watts	
Function 4 Position Dimmer 0, 10, 20, 50 & 100% using PWM	

Unit Diagram



Safety Information:

- 1. Supply Voltage of this product is 12 VDC, Do not exceed.
- 2. Sorting Output wires may cause damage to dimmer.
- 3. Always observe proper polarity when connecting power and load.
- 4. For indoor use only – This product is not waterproof or weatherproof.

Note: If the Dimmer does not function check that the power is plugged into the POWER IN connector.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Inspired LED:

4821