

Proheat® Heat Gun, Kit & Accessories

Rugged dual temperature heat gun

- New 230 Volt CE Certified model available with four cordset options
- Compact, lightweight, easy-to-use
- Balanced ergonomic design prevents operator fatigue
- Two heat settings 430°F or 840°F (221°C or 449°C)
- Base provides built-in stand for hands-free use
- Protective hand/switch guard and hanging loop
- UL Listed or CE Certified, Made in USA
- Use to activate adhesives, bend plastics, dry filler material, shrink tubing and more



PH-1100
PH-2100



35016



35017



35216



35026



35351

MODEL NO.	DESCRIPTION									
PH-1100	430°F or 840°F	221°C or 449°C	15 CFM	120V	60 Hz	11A	656 or 1300W	CE	UL	US
PH-1100K	430°F or 840°F	221°C or 449°C	15 CFM	120V	60 Hz	11A	656 or 1300W	CE	UL	US
	with storage case and 2 attachments (35016 and 35017)									
PH-2100	430°F or 840°F	221°C or 449°C	16 CFM	230V	50/60 Hz	6.2A	705 or 1410W	CE	UL	US
PH-2100K	430°F or 840°F	221°C or 449°C	16 CFM	230V	50/60 Hz	6.2A	705 or 1410W	CE	UL	US
	with storage case and all 2 attachments (35016 and 35017)									

Optional Accessories

PART NO.	DESCRIPTION	PART NO.	DESCRIPTION
35016	3-1/2" spreader attachment	35026	Nozzle shield
35017	1-3/8" heat shrink attachment	35351	Storage/carrying case
35216	Bench stand		

Specifications

■ Air Volume: 15 CFM ■ Air Velocity: 3584 FPM (PH-1100), 4000 FPM (PH-2100) ■ Motor: Permanent Magnet ■ Nozzle Opening: .88" I.D., 1.31" O.D.
 ■ Cordset: 6 ft., 3-wire grounded ■ Dimensions: 8.2" L x 3.0" W x 7.3" H ■ Tool Net Weight: 1.6 lbs. ■ Shipping Weight Tool: 2 lbs. ■ Shipping Weight Kit: 7 lbs.

NOTE: Users should independently evaluate the suitability of the product for their application.



Proheat with rugged storage case and 2 specialty attachments



Replacement Heating Element
 120V 35004
 220V 35022



Heat Adhesives



Strip Paint



Loosen Bolts