


CATALOG LISTING
10BS211
PAGE 1 OF 1
RELEASE NO. PR-2484
ISSUE 12
CHECK
REVISIONS
A 205627
CSL 22 MAY 02
CHECK
22 MAY 02
SAV
CHECK
22 MAY 02
DRAWN
RASTER



- NOTES**
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS
 - 2 - DIAL WHEEL IS SHOWN AT THE MAX SETTING OF BREAK DISTANCE
 - 3 - DIAL WHEEL ROTATION 300°

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		THIRD ANGLE PROJECTION	
CHARACTERISTICS		ELECTRICAL DATA	SCALE FULL
AT MIN SETTING OPERATING FORCE ----- 11-20 OZ RELEASE FORCE ----- 10 OZ MIN DIFFERENTIAL TRAVEL ----- .0015-.0025		CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
AT MAX SETTING DIFFERENTIAL TRAVEL ----- .007 MIN OVERTRAVEL ----- .010 MIN		L17 20A 125, 250 OR 480 VAC 3/4HP 125 VAC, 1 1/2HP 250 VAC	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
			WEIGHT