


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL CHECK IN	01/30/04	M.CCORMICK
B	ECN# 2731 - ADDED ROHS STAMP	10/23/07	D.GRIFFIN
C	ECN 3957: CHANGE MATL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO
D	ECN 4278: ADDED OPERATING TEMPERATURE RANGE AND PACKAGING	10/1/09	D.FRISIELLO



NOTES:

1. RECOMMENDED CABLE DIAMETER: .138 ϕ THRU .276 ϕ
2. IP (INGRESS PROTECTION) RATING: 67.
3. OPERATING TEMPERATURE RANGE: -40 °C TO +105 °C.
4. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


MATERIAL:

GASKETS: EPDM
BODY: NYLON
HOUSING: ABS
O-RING: SILICONE
SEAL: EPDM
SEALING NUT: NYLON
THUMBSCREW: BRASS

FINISH:

THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ± 1 .XX = $\pm .02$.XXX = $\pm .005$ ANGULAR TOLERANCES: ALL = $\pm 1^\circ$	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	01/28/2004		
	CHECKED BY D.PARHAM	01/28/2004	CATEGORY	
	APPROVED BY R.CARRICK	01/28/2004	PRODUCT DESCRIPTION	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		DB9 MALE WATERPROOF CONNECTOR	
COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. WPDB9P-KIT
REF		SCALE: NONE	CAD FILE: WPDB9P-KIT.SLDDRW	REV. D
		SHEET 1 OF 1		